


# Horizontal Rail, Front, Type L-KD, Light, Short Lip, 28 HP

## CATALOG NUMBER

**34560-128**



Combinations of horizontal rails and side panels

|                                                            | Standard rail | Standard rail with short lip | Standard rail with short lip and rear panel | Standard rail with short lip and rear panel and side panel |
|------------------------------------------------------------|---------------|------------------------------|---------------------------------------------|------------------------------------------------------------|
| Standard rail                                              | -             | +                            | +                                           | +                                                          |
| Standard rail with short lip                               | +             | +                            | +                                           | +                                                          |
| Standard rail with short lip and rear panel                | +             | +                            | -                                           | -                                                          |
| Standard rail with short lip and rear panel and side panel | +             | +                            | -                                           | -                                                          |

Legend: + can be combined, - combination not recommended

The horizontal rail with a short lip makes a clean design to the assembled front panel.

## CERTIFICATIONS



## FEATURES

Standard rail at the front

Installation at top and bottom

Short lip (L-KD)

< 28 HP not to print

Aluminum extrusion, anodized finish, conductive contact surface

## PRODUCT ATTRIBUTES

Rack Width: 28HP

Package Quantity: 1

Finish: Anodized

Length: 147.32mm

Material: Aluminum

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Light, KD

Works With: Subracks; Cases

Gross Weight: 0.048kg

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**