

# Cable to Web of Rail Mold Only, Signal

## Data Solutions



### FEATURES

Replacement mold designed for the installation of track circuits and jumper bonds to the neutral axis

### SPECIFICATIONS

**Rail Type:** 85 lb to 141 lb T-Rail Sections

**Material:** Graphite

Table 1/1

| Catalog Number | Bond Terminal Style | Conductor Size                   | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|----------------|---------------------|----------------------------------|-----------------------------------|--------------|-------------|
| SBB200CLH      | 1" Tab              | 3/16" Bondstrand                 | 4.76mm                            | TB5, T21     | Left Hand   |
| SBB200CRH      | 1" Tab              | 3/16" Bondstrand                 | 4.76mm                            | TB5, T21     | Right Hand  |
| SBW3150BLH     | 1" Tab              | 3/16" Bondstrand                 | 4.76mm                            | TB5          | Left Hand   |
| SBW3150BRH     | 1" Tab              | 3/16" Bondstrand                 | 4.76mm                            | TB5          | Right Hand  |
| SBB200YLH      | 1" Tab              | 16 mm <sup>2</sup><br>Concentric | 5.18mm                            | T21, TB5     | Left Hand   |

| Catalog Number | Bond Terminal Style | Conductor Size                | Conductor Outer Diameter, Nominal | Welder Style | Orientation |
|----------------|---------------------|-------------------------------|-----------------------------------|--------------|-------------|
| SBB200YRH      | 1" Tab              | 16 mm <sup>2</sup> Concentric | 5.18mm                            | T21, TB5     | Right Hand  |
| SBB200XRH      | 1" Tab              | 25 mm <sup>2</sup> Stranded   | 6.6mm                             | TB5, T21     | Right Hand  |
| SBB200PLH      | 1" Tab              | 35 mm <sup>2</sup> Stranded   | 7.75mm                            | TB5, T21     | Left Hand   |
| SBB200PRH      | 1" Tab              | 35 mm <sup>2</sup> Stranded   | 7.75mm                            | TB5, T21     | Right Hand  |
| SBWW6LH        | Field-made          | 50 mm <sup>2</sup> Solid      | 8mm                               | T21          | Left Hand   |
| SBWW6RH        | Field-made          | 50 mm <sup>2</sup> Solid      | 8mm                               | T21          | Right Hand  |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**