


DT Panel Protector (F), 120 kA

Data Solutions



The nVent ERICO DTX120 Series of Surge Protective Devices (SPD) features North American and Worldwide standards compliance and provides premium protection against damaging transients and surge currents, particularly in IEC Class I & Class II and UL Type 1 & Type 2 locations. The innovative design allows for installation on the line or load of the service panels and removes the need for circuit breakers (B Version Only). With a 120 kA per phase surge rating, DTX120 is well suited for category C locations. It is typically used in applications including service entrances, distribution, branch panels, MCC, lighting panels, HVAC, and more. The nVent ERICO DTX120 also features a NEMA®-4X enclosure rating, making it suitable for outdoor applications.

CERTIFICATIONS



FEATURES

Excellent clamping and low UL voltage protection ratings

Features relay alarming for power/phase loss and status of SPD health

Design allows for easy removal and replacement of surge modules via lever assist

RS-485 Interface Standard

Up to 53 dB attenuation (10 kHz to 100 MHz)

10 Year Warranty

SPECIFICATIONS

Catalog Number	DTX120F12024 OSP	DTX120F12024 OHD	DTX120F208Y	DTX120F240D	DTX120F480D	DTX120F480Y
----------------	---------------------	---------------------	-------------	-------------	-------------	-------------

Nominal System Voltage (Un)	120/240 V	120/240 V	120/208 V	240 VAC	480 V	277/480 V
Distribution System	1Ph 3W+G	3PhΔ 4W+G	3Ph 4W+G	3PhΔ 3W+G	3PhΔ 3W+G	3Ph 4W+G
Max Continuous Operating Voltage (Uc)	150/300 VAC	150/275 VAC	150/300 VAC	275 VAC	510 VAC	350/700 VAC
Max Discharge Current (Imax), Per Phase	120kA 8/20 μs	120kA 8/20 μs	120kA 8/20 μs	120kA 8/20 μs	120kA 8/20 μs	120kA 8/20 μs
Impulse Current (Iimp), Per Mode	12.5kA 10/350 μs	12.5kA 10/350 μs	12.5kA 10/350 μs	12.5kA 10/350 μs	12.5kA 10/350 μs	12.5kA 10/350 μs
Filtering	-29 dB @ 100 kHz	-29 dB @ 100 kHz	-29 dB @ 100 kHz	-29 dB @ 100 kHz	-29 dB @ 100 kHz	-29 dB @ 100 kHz
Frequency	50 – 60Hz	50 – 60Hz	50 – 60Hz	50 – 60Hz	50 – 60Hz	50 – 60Hz
Voltage Protection Rating (VPR), L-G	700V	1200V	700V	1000V	1800V	1200V
Voltage Protection Rating (VPR), L-L	1000V	1500V	1200V	1000V	1800V	2000V
Voltage Protection Rating (VPR), L-N	700V	800V	700V			1200V
Voltage Protection Rating (VPR), N-G	700V	1500V	600V			1200V
Protection Modes	L-PE L-PE N-PE	L-N L-PE N-PE	L-N L-PE N-PE	L-PE	L-PE	L-N L-PE N-PE
Short Circuit Current Rating (SCCR)	200kA	200kA	200kA	200kA	200kA	200kA
Nominal Discharge Current (In), IEC	40kA 8/20 μs	40kA 8/20 μs	40kA 8/20 μs	40kA 8/20 μs	40kA 8/20 μs	40kA 8/20 μs
Nominal Discharge Current (In), UL	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs	20kA 8/20 μs


Voltage Protection Level (Up), IEC	1200 V @ 20 kA 3000 V @ 100 kA	1200 V @ 20 kA 3000 V @ 100 kA	1200 V @ 20 kA 3000 V @ 100 kA	1200 V @ 20 kA 3000 V @ 100 kA	1200 V @ 20 kA 3000 V @ 100 kA	1200 V @ 20 kA 3000 V @ 100 kA
Short Circuit Current Rating (Iscrr)	50kA	50kA	50kA	50kA	50kA	50kA
Temperature	-40 to 80°C	-40 to 80°C	-40 to 80°C	-40 to 80°C	-40 to 80°C	-40 to 80°C
Enclosure Material	Metal with PC Lid	Metal with PC Lid	Metal with PC Lid	Metal with PC Lid	Metal with PC Lid	Metal with PC Lid
Enclosure Rating	NEMA®-4X UL® 50E Type 4	NEMA®-4X UL® 50E Type 4	NEMA®-4X UL® 50E Type 4	NEMA®-4X UL® 50E Type 4	NEMA®-4X UL® 50E Type 4	NEMA®-4X UL® 50E Type 4
Lead Size	2.5 – 16mm ²	2.5 – 16mm ²	2.5 – 16mm ²	2.5 – 16mm ²	2.5 – 16mm ²	2.5 – 16mm ²
Mounting	4 Screw Locations	4 Screw Locations	4 Screw Locations	4 Screw Locations	4 Screw Locations	4 Screw Locations
Remote Contact Switching Capacity	2.0 A @ 240 V	2.0 A @ 240 V	2.0 A @ 240 V	2.0 A @ 240 V	2.0 A @ 240 V	2.0 A @ 240 V
Remote Contacts	Yes (Form C)	Yes (Form C)	Yes (Form C)	Yes (Form C)	Yes (Form C)	Yes (Form C)
Status Indication	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable	Audible alarm with silence switch Dual color status LED Mechanical flag OLED Display Surge/TOV Counter, Resettable
Technology	Hybrid technology utilizing thermal disconnects	Hybrid technology utilizing thermal disconnects	Hybrid technology utilizing thermal disconnects	Hybrid technology utilizing thermal disconnects	Hybrid technology utilizing thermal disconnects	Hybrid technology utilizing thermal disconnects
Certification Details	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode	CSA C22.2 No. 269.2 UL® 1283 Edition 7 UL® 1449 Edition 5 Type 2, 20 kA Mode

Complies With	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II	ANSI®/IEEE® C62.41.1-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C ANSI®/IEEE® C62.45-2002 Cat A, Cat B, Cat C EN 61643-11 Type 2 IEC® 61643-11 Class II
Depth (D)	98.3mm	98.3mm	98.3mm	98.3mm	98.3mm	98.3mm
Height (H)	330.7mm	330.7mm	330.7mm	330.7mm	330.7mm	330.7mm
Width (W)	101.6mm	101.6mm	101.6mm	101.6mm	101.6mm	101.6mm
Unit Weight	2.9kg	2.7kg	2.86kg	2.79kg	2.88kg	3.08kg
Replacement Module	DT2180DTXM DT2275DTXM	DT2180DTXM DT2275DTXM	DT2150DTXM	DT2275DTXM	DT2510DTXM	DT2350M

ADDITIONAL PRODUCT DETAILS

Optional Flush Plate and Side Mount Kits available: DTX120FP & DTX120SM

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE