


Outdoor Comline FTTX Cabinet With Dual Access, 1200H 800W 600D

Data Solutions

CATALOG NUMBER

12349-008



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

CERTIFICATIONS



FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

PRODUCT ATTRIBUTES

Product Type: Outdoor Cabinet
Product Family: Comline FTTX
Rack Height: 25U
Height: 1200mm
Width: 800mm
Depth: 600mm
Wall Type: Single Walled
Door Type: Single Door
Access: Front; Back
Cooling: Insulation
EMC Shielding: No
Complies With: IEC 61969-1; IEC 61969-2; IEC 60917-1; IEC 60917-2; ETS 300119; IEC 60529; DIN EN 50178; VDE 0160
Package Quantity: 1
Finish: Powder Coated
Material: Aluminum
Net Weight: 68kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE