


# nVent ERICO Cadweld One Shot for Rail, Cable to Cable



nVent ERICO Cadweld applications for railway properties utilize the nVent ERICO Cadweld Plus F80 and the nVent ERICO Cadweld F80 welding material alloys. nVent ERICO Cadweld exothermically welded connections are engineered to provide a permanent, molecular bond that will not loosen or corrode, enabling connection of dissimilar materials. The connections are designed to perform for the life of the conductor and/or installation. The nVent ERICO Cadweld connection has a current carrying capacity equal to or greater than that of the conductor and will withstand repeated fault currents without failing during operation. Once completed, installers can clearly ensure quality by visually inspecting the new connection.

## DIAGRAMS



## FEATURES

For use with rail applications

Single use ceramic mold which eliminates the need for a graphite mold and handle clamp/frame (T320 flint igniter not included)

Produces a permanent connection that will not loosen or corrode

Supplied with F80 welding material

NEC® compliant


## SPECIFICATIONS

Table 1/1

| Catalog Number | Welding Material Type | Mold Family | Conductor 1            | Conductor 2            |
|----------------|-----------------------|-------------|------------------------|------------------------|
| SBPG11L        | Traditional           | PG          | #6 Stranded - #3 Solid | #6 Stranded - #3 Solid |

| Catalog Number | Welding Material Type    | Mold Family | Conductor 1            | Conductor 2            |
|----------------|--------------------------|-------------|------------------------|------------------------|
| SBPG11LPLUS    | nVent ERICO Cadweld Plus | PG          | #6 Stranded - #3 Solid | #6 Stranded - #3 Solid |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE