

# Cable Entry Gland Plate Hole Punch, CEAP

CEAP punching tools for CCF and CEP cable entry systems.



## FEATURES

---

Delivery: Stamp, die, pull axis, lock nut, plastic case.

Pack quantity: 1 pcs.

Material: 2 mm maximum thickness for S 235 sheet metal.

Description: By using the CEAP sheet metal punching tool, the desired breakout can be made precisely without chips or splintering in only a few minutes. The convenient built-in punch-hole marking tip can be used to punch-mark the drill points clearly for screw-on attachments. These sheet-metal punches are compatible with all common hydraulic pumps.

SPECIFICATIONS

| Table 1/1      |                |        |         |       |                  |            |
|----------------|----------------|--------|---------|-------|------------------|------------|
| Catalog Number | Article Number | Height | Width   | Depth | Product Family   | Material   |
| CEAP14         | 58379          | 71mm   | 71mm    | 50mm  | Cable management | Mild Steel |
| CEAP01-CEP     | 58384          | 61mm   | 137mm   | 50mm  | Cable management | Mild Steel |
| CEAP610        | 58381          | 71mm   | 93.5mm  | 50mm  | Cable management | Mild Steel |
| CEAP816        | 58382          | 71mm   | 116mm   | 50mm  | Cable management | Mild Steel |
| CEAP1024       | 58383          | 71mm   | 138.5mm | 50mm  | Cable management | Mild Steel |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE