

nVent LENTON Quick Wedge Replacement Pin

Wedge pins are provided with the purchase of couplers. Replacement wedge pins are made available as a convenience, should any get lost on the jobsite.



FEATURES

Package comes with twenty-six replacement wedge pins and one grommet

Designed to withstand the forces required for assembly

SPECIFICATIONS

Material: Steel

Table 1/2

| Catalog Number | Article Number | Finish | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) |
|----------------|----------------|-----------------------|--------------------|----------------|--------------------|--------------|
| ML4GPKG26 | | Mechanical Galvanized | 12 mm | #4 | 10M | 13 mm |
| ML4PKG26 | 145860 | Plain | 12 mm | #4 | 10M | 13 mm |
| ML5GPKG26 | | Mechanical Galvanized | 16 mm | #5 | 15M | 13 mm |
| ML5PKG26 | 145870 | Plain | 16 mm | #5 | 15M | 13 mm |
| ML6GPKG26 | | Mechanical Galvanized | 20 mm | #6 | 20M | 16 mm |
| ML6PKG26 | 145880 | Plain | 20 mm | #6 | 20M | 16 mm |


Table 2/2

| Catalog Number | Article Number | Length (L) | Unit Weight |
|----------------|----------------|------------|-------------|
| ML4GPKG26 | | 40mm | 0.03 kg |
| ML4PKG26 | 145860 | 40mm | 0.03 kg |
| ML5GPKG26 | | 46mm | 0.04 kg |
| ML5PKG26 | 145870 | 46mm | 0.04 kg |
| ML6GPKG26 | | 53mm | 0.06 kg |
| ML6PKG26 | 145880 | 53mm | 0.06 kg |

ADDITIONAL PRODUCT DETAILS

Prior to installation, please read and understand the detailed instructions and safety notices provided in the nVent LENTON Quick Wedge Operator's Manual.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE