

# Outdoor Comline FTTX Cabinet



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

## CERTIFICATIONS



## FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

## SPECIFICATIONS

**Material:** Aluminum

Table 1/3

| Catalog Number | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|----------------|-----------------|----------------|-------------|--------|-------|-------|
| 12349-006      | Outdoor Cabinet | Comline FTTX   | 25U         | 1200mm | 800mm | 600mm |
| 12349-005      | Outdoor Cabinet | Comline FTTX   | 12U         | 600mm  | 800mm | 600mm |

| CatalogNumber | Product Type    | Product Family | Rack Height | Height | Width | Depth |
|---------------|-----------------|----------------|-------------|--------|-------|-------|
| 12349-007     | Outdoor Cabinet | Comline FTTX   | 12U         | 600mm  | 800mm | 600mm |
| 12349-008     | Outdoor Cabinet | Comline FTTX   | 25U         | 1200mm | 800mm | 600mm |

Table 2/3

| Catalog Number | Wall Type     | Door Type   | Access      | Cooling    | EMC Shielding | Complies With                                                                                     |
|----------------|---------------|-------------|-------------|------------|---------------|---------------------------------------------------------------------------------------------------|
| 12349-006      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-005      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-007      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |
| 12349-008      | Single Walled | Single Door | Front, Back | Insulation | No            | IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160 |

Table 3/3

| Catalog Number | Package Quantity | Finish        | Quick Ship |
|----------------|------------------|---------------|------------|
| 12349-006      | 1                | Powder Coated | No         |

| Catalog Number | Package Quantity | Finish        | Quick Ship |
|----------------|------------------|---------------|------------|
| 12349-005      | 1                | Powder Coated | No         |
| 12349-007      | 1                | Powder Coated | No         |
| 12349-008      | 1                | Powder Coated | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE