


# Panhead Screw, Torx, Self-Securing



Pan head torx screws with different metric threads and lengths. With optional features like GND earthing function or precoded thread.

## **CERTIFICATIONS**



## **FEATURES**

Pan Head Screw with torx, self-locking

## **SPECIFICATIONS**

**Type:** Panhead Screw

**Product Type:** Screw **Material:** Steel

Table 1/1						
Catalog Number	Length	Finish	Package Quantity	Thread Size	Works With	Quick Ship
24560-159	6mm	Zinc Plated	100	M2.5	Backplanes, Test Adapters	No
21500-039	9.3mm	Zinc Plated	100	M2.5	Front Panels, Horizontal Rails, Type H, Horizontal Rails, Type R	No

Torque max. 0.2 Nm.

#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### **North America**

All locations +1.763.422.2661 Chat with us: nvent.com/schroff

## Europe

Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff

## Asia

Shanghai, China

+86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff

## Middle East & India

Dubai, United Arab **Emirates** +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**