

Varistar CP Seismic Base/Plinth

A plinth allows functional storage of excess cable assemblies and protects the bottom part of the cabinet against rodents.



FEATURES

2 support profiles, St, 10 mm, side

Seismic dynamic load-carrying capacity 500 kg

Height 103 mm

2 covers, St, 10 mm, front and rear

Conforms to NEBS, Earthquake secure (up) to Bellcore Zone 4, tested with 500 KGs, Mounting holes for fitting of base

Access possible from front and rear

SPECIFICATIONS

Static Load: 400kg
Product Type: Cabinet/Rack Base
Material: Steel

Table 1/2

Catalog Number	Width	Depth	Package Quantity	Color	Color Code	Complies With
21630-110	600mm	600mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-111	600mm	800mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-112	600mm	1000mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

CatalogNumber	Width	Depth	Package Quantity	Color	Color Code	Complies With
21630-113	600mm	1200mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-114	800mm	600mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-115	800mm	800mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-116	800mm	1000mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-117	800mm	1200mm	1	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Catalog Number	Finish	Height	Type	Works With	Quick Ship
21630-110	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-111	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-112	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-113	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-114	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-115	Powder Coated	103mm	Base Plinth	Varistar CP	No
21630-116	Powder Coated	800mm	Base Plinth	Varistar CP	No
21630-117	Powder Coated	103mm	Base Plinth	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE