


Theft-Deterrent Grounding Busbar, Wall Mount Assembly



CERTIFICATIONS



FEATURES

Utilizes a utility or telecom tower's or other mounting structure's connection to a ground ring to provide equipotential bonding and a low-impedance path to ground

Can be used for any mounting application and in any configuration

Accepts standard telecommunication grounding lugs (lugs not included)

Includes 17 Standard Spacers (TDSGAS)

SPECIFICATIONS


Table 1/2

Catalog Number	Material	Finish	Spacer Thickness	Length 1 (L1)	Length 2 (L2)	Width (W)
----------------	----------	--------	------------------	---------------	---------------	-----------

TDSGAWB17	Copper, Aluminum, Stainless Steel 304 (EN 1.4301), Stainless Steel 18-8 (EN 1.4305), Nylon	Tinned	6.4mm	235 mm	38.1 mm	50.8 mm
-----------	---	--------	-------	--------	---------	---------

Table 2/2				
Catalog Number	Height (H)	A	Hole Size (HS)	Thread Size (TS)
TDSGAWB17	50.8 mm	25.4 mm	9.8 mm	3/8" UNC

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

North America +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support	Europe Netherlands: +31 800-0200135 France: +33 800 901 793	Europe Germany: 800 1890272 Other Countries: +31 13 5835404	APAC Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500
---	--	--	--



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE