

# Gland plate with knockouts, AFK



The required number of holes for cable entries can be easily knocked out of this steel gland plate to allow for the cabling required.

## FEATURES

Description: Gland plates with knock-outs according to table.

Material: 1.4 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece.

## SPECIFICATIONS

|                    |               |
|--------------------|---------------|
| <b>Thickness:</b>  | 1.4mm         |
| <b>Color:</b>      | Light Gray    |
| <b>Material:</b>   | Mild Steel    |
| <b>Finish:</b>     | Powder Coated |
| <b>Color Code:</b> | RAL 7035      |

Table 1/1

| Catalog Number | Article Number | Height | Width | Depth | Knockout Pattern                           | Gland Plate Type |
|----------------|----------------|--------|-------|-------|--------------------------------------------|------------------|
| AFK11R5        | AFK11R5        | 242mm  | 128mm | 3mm   | (4) M16, (5) M20,<br>(2) M25, (2) M32      | 1                |
| AFK11SR5       | AFK11SR5       | 242mm  | 88mm  | 3mm   | (4) M16, (3) M20                           | 1S               |
| AFK21R5        | AFK21R5        | 342mm  | 128mm | 3mm   | (9) M16, (5) M20,<br>(4) M25, (2) M32      | 2                |
| AFK21SR5       | AFK21SR5       | 342mm  | 88mm  | 3mm   | (6) M16, (3) M20,<br>(1) M25               | 2S               |
| AFK31R5        | AFK31R5        | 442mm  | 128mm | 3mm   | (18) M16, (5)<br>M20, (4) M25, (2)<br>M32  | 3                |
| AFK31SR5       | AFK31SR5       | 442mm  | 88mm  | 3mm   | (9) M16, (4) M20,<br>(1) M25               | 3S               |
| AFK41R5        | AFK41R5        | 542mm  | 128mm | 3mm   | (27) M16, (5)<br>M20, (4) M25, (2)<br>M32  | 4                |
| AFK42R5        | AFK42R5        | 542mm  | 88mm  | 3mm   | (18) M16, (14)<br>M20, (3) M25, (1)<br>M32 | 4                |
| AFK12R5        | AFK12R5        | 242mm  | 128mm | 3mm   | (12) M16, (1)<br>M25, (1) M32              | 1                |
| AFK22R5        | AFK22R5        | 342mm  | 128mm | 3mm   | (21) M16, (1)<br>M32, (1) M25              | 2                |
| AFK32R5        | AFK32R5        | 442mm  | 128mm | 3mm   | (21) M16, (10)<br>M20                      | 3                |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**