

# Varistar CP Base/Plinth Side

## Power Utilities

Sides trim to mount to Varistar CP base/plinth

### FEATURES

Base/plinth sides, plain

### SPECIFICATIONS

Table 1/2

| Catalog Number | Height | Depth   | Package Quantity | Color      | Color Code | Finish        |
|----------------|--------|---------|------------------|------------|------------|---------------|
| 24630-038      | 100 mm | 1000 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-039      | 100 mm | 1100 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-040      | 100 mm | 1200 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-041      | 200 mm | 1000 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-042      | 200 mm | 1100 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-043      | 200 mm | 1200 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-077      | 100 mm | 600 mm  | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-078      | 100 mm | 800 mm  | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-079      | 100 mm | 900 mm  | 1                | Black Grey | RAL 7021   | Powder Coated |

| CatalogNumber | Height | Depth  | Package Quantity | Color      | Color Code | Finish        |
|---------------|--------|--------|------------------|------------|------------|---------------|
| 24630-080     | 200 mm | 600 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-081     | 200 mm | 800 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-082     | 200 mm | 900 mm | 1                | Black Grey | RAL 7021   | Powder Coated |
| 24630-083     | 100 mm | 300 mm |                  | Black Grey | RAL 7021   | Powder Coated |
| 24630-084     | 200 mm | 300 mm |                  | Black Grey | RAL 7021   | Powder Coated |

Table 2/2

| Catalog Number | Material | Product Type      | Type        | Package Unit |
|----------------|----------|-------------------|-------------|--------------|
| 24630-038      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-039      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-040      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-041      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-042      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-043      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-077      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-078      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-079      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-080      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-081      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |
| 24630-082      | Steel    | Cabinet/Rack Base | Plinth Side | Pair         |

| Catalog Number | Material | Product Type      | Type        | Package Unit |
|----------------|----------|-------------------|-------------|--------------|
| 24630-083      | Steel    | Cabinet/Rack Base | Plinth Side |              |
| 24630-084      | Steel    | Cabinet/Rack Base | Plinth Side |              |

### ADDITIONAL PRODUCT DETAILS

Please order base/plinth for front/rear separately.

Cannot be used in conjunction with castors

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE