

XL-Trace Contractor Pack, Low Smoke Zero Halogen Self-Regulating Cable Kit



nVent RAYCHEM contractor packs comprise a fixed length of heating cable supplied in an easy-to-use and carry spool box. The spool allows the installer to feed out the required length easily, reducing installation time and effort.

FEATURES

Unparalleled safety, low smoke zero halogen construction: up to 90% less smoke emissions and improved self-extinguishing properties

Zero halogen: IEC60754-1 tested and compliant

Improved self-extinguishing properties under the IEC62395 flammability test

Energy efficient: self-regulating cable, major savings when used with proportional ambient sensing controller (PASC), no cable overheating possible

Self-regulating technology: cut-to-length on site to mitigate any design variations

Quick and easy installation with the RayClic fast connection system

SPECIFICATIONS

Nominal Height:	6.8 mm
Nominal Width:	13.8 mm
Supply Voltage:	220 – 240 V
Min Installation Temperature:	-40 °C
Ground Path Type:	Braid
Outer Jacket Material:	Low Smoke Zero Halogen
Heating Cable Technology:	Self-Regulating

Table 1/1

Catalog Number	Item Name	Length	Nominal Power Output @ 5°C, 230V	Max Continuous Exposure Temperature, Power On	Color
1244-021262	XL-Trace-InstallerPack-10XL-30m	30 m	10 W/m	65 °C	Plum
1244-021263	XL-Trace-InstallerPack-10XL-50m	50 m	10 W/m	65 °C	Plum
1244-021264	XL-Trace-InstallerPack-10XL-80m	80 m	10 W/m	65 °C	Plum
1244-021265	XL-Trace-InstallerPack-15XL-50m	50 m	15 W/m	65 °C	Green
1244-021266	XL-Trace-InstallerPack-15XL-80m	80 m	15 W/m	65 °C	Green
1244-021267	XL-Trace-InstallerPack-26XL-50m	50 m	26 W/m	65 °C	Blue
1244-021268	XL-Trace-InstallerPack-26XL-80m	80 m	26 W/m	65 °C	Blue
1244-021269	XL-Trace-InstallerPack-31XL-50m	50 m	31 W/m	85 °C	Purple
1244-021270	XL-Trace-InstallerPack-31XL-80m	80 m	31 W/m	85 °C	Purple

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Latin America

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT