

Outdoor Comline FTTX Cabinet



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

CERTIFICATIONS



FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

SPECIFICATIONS

Material: Aluminum

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Height	Width	Depth
12349-007	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm
12349-006	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm

CatalogNumber	Product Type	Product Family	Rack Height	Height	Width	Depth
12349-005	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm
12349-008	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm

Table 2/3

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-007	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-006	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-005	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-008	Single Walled	Single Door	Front, Back	Insulation	No	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Catalog Number	Package Quantity	Finish	Quick Ship
12349-007	1	Powder Coated	No

Catalog Number	Package Quantity	Finish	Quick Ship
12349-006	1	Powder Coated	No
12349-005	1	Powder Coated	No
12349-008	1	Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE