

# Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking



EMC and IP55 Steel Door with lever handle and 4-Point locking.

## FEATURES

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

## SPECIFICATIONS

**Product Type:** Cabinet Door

**Protection Rating:** IP55

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Package Quantity | Complies With                                             | Finish        |
|----------------|-------------|--------|-------|------------------|-----------------------------------------------------------|---------------|
| 21630-760      | 33U         | 1600mm | 600mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-761      | 33U         | 1600mm | 800mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |

| CatalogNumber | Rack Height | Height | Width | Package Quantity | Complies With                                             | Finish        |
|---------------|-------------|--------|-------|------------------|-----------------------------------------------------------|---------------|
| 21630-762     | 38U         | 1800mm | 600mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-763     | 38U         | 1800mm | 800mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-764     | 42U         | 2000mm | 600mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-765     | 42U         | 2000mm | 800mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-766     | 47U         | 2200mm | 600mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |
| 21630-767     | 47U         | 2200mm | 800mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3,<br>IEC 60529 | Powder Coated |

Table 2/2

| Catalog Number | Locking Type    | Type              | Works With  | Quick Ship |
|----------------|-----------------|-------------------|-------------|------------|
| 21630-760      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-761      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-762      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-763      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-764      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-765      | 4-Point Locking | Steel Door, Plain | Varistar CP | No         |
| 21630-766      | 5-Point Locking | Steel Door, Plain | Varistar CP | No         |

| Catalog Number | Locking Type    | Type              | Works With  | Quick Ship |
|----------------|-----------------|-------------------|-------------|------------|
| 21630-767      | 5-Point Locking | Steel Door, Plain | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**