


Internal Channel Connector



SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	Material	Finish	Hole Size (HS)	Hole Spacing	Length (L)
ZUA408	387830	Steel	Hot-Dip Galvanized	12 mm	54mm	203mm

Table 2/2

Catalog Number	Article Number	Width (W)	Thickness (T)
ZUA408	387830	35 mm	10 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

