

# nVent CADDY Cat HP J-Hook with Hammer-On Flange Clip, Swivel



#### **CERTIFICATIONS**





### **FEATURES**

Requires only a hammer to install

Rotates 360 degrees to support various directional runs of cable

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Rounded edges on J-Hooks provide proper bend radius support for high performance data cables

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

#### **SPECIFICATIONS**

Finish: Pregalvanized;nVent CADDY Armour

**Material:** Steel;Spring Steel

Table 1/2							
Catalog Number	Article Number	Diameter (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	
CAT48HP24	181215	75 mm	5974mm²	200	150	80	
CAT32HP24	181214	50 mm	2561mm²	90	60	35	
CAT64HP24	181216	100 mm	9987mm²	330	220	140	
CAT48HP58	181231	75 mm	5974mm²	200	150	80	
CAT16HP58	181001	25 mm	690mm²	20	15	10	

Table 2/2							
Catalog Number	Article Number	Flange Thickness (FT)	Static Load				
CAT48HP24	181215	3 - 8 mm	270N				
CAT32HP24	181214	3 - 8 mm	270N				
CAT64HP24	181216	3 - 8 mm	270N				
CAT48HP58	181231	8 - 14 mm	270N				
CAT16HP58	181001	8 - 14 mm	270N				

## ADDITIONAL PRODUCT DETAILS

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

#### **DIAGRAMS**



#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America** 

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

Europe

Germany: 800 1890272 Other Countries: +31 13 5835404 APAC

Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500



Our powerful portfolio of brands:

**CADDY** 

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

**TRACHTE** 

