

Cable to Web of Rail T21 Complete Welder, Signal, 1" Tab Bond Terminal Style, 16 mm² Concentric, Right Hand

Data Solutions

CATALOG NUMBER

SBTBT21YRH



FEATURES

Complete right hand or left hand web welder assembly designed for the installation of track circuits and jumper bonds to the neutral axis of 85 to 141 lb. rail

Includes mold cleaner and flint ignitor

PRODUCT ATTRIBUTES

Material: Steel; Graphite

Rail Type: 85 lb to 141 lb T-Rail Sections

Bond Terminal Style: 1" Tab

Conductor Size: 16 mm² Concentric

Conductor Outer Diameter, Nominal: 5.18mm

Welder Style: T21

Orientation: Right Hand

Mold Only: No

Replacement Mold: SBB200YRH

Welding Material: SB25, Sold Separately

Handle Clamp: C105B, Sold Separately

Conductor Sleeve: SBS12C, Sold Separately

Bond Clip: S2659, Included

Hammer Die: SBD50, Sold Separately

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRachte