

# nVent CADDY Cat HP J-Hook Clip to BC Beam Clamp

## Data Solutions



### CERTIFICATIONS



### FEATURES

Easy installation to beam flanges

Requires no screws, rivets or special tools for assembly

J-Hooks feature bendable locking tabs that lock on to nVent CADDY Cat HP components to provide rigidity and stability

Link to J-Hooks in one of multiple color options to aid in pathway identification and organization

Customized J-Hook trees can be easily assembled with various J-Hook sizes, colors and configurations

nVent CADDY Cat HP components easily attach to any size nVent CADDY Cat HP J-Hook


### SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | Material | Finish | Flange Thickness (FT) | Static Load |
|----------------|----------------|----------|--------|-----------------------|-------------|
|----------------|----------------|----------|--------|-----------------------|-------------|

|         |        |                     |                                             |            |      |
|---------|--------|---------------------|---------------------------------------------|------------|------|
| CATHPBC | 181078 | Steel, Spring Steel | Electrogalvanized,<br>nVent CADDY<br>Armour | 3.2 – 16mm | 440N |
|---------|--------|---------------------|---------------------------------------------|------------|------|

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE