

Inspection Housing with Conduit Cutout, High Density Polyethylene (HDPE)



FEATURES

Suitable for lighter load rating applications in turf

Chemical, UV and corrosion resistant

SPECIFICATIONS

Table 1/2

Catalog Number	Material	Color	Load Rating	Diameter, Grade Level (DG)	Outer Diameter (OD)	Height (H)
T416C	High Density Polyethylene (HDPE)	Black	0.15kPa	362mm	619 mm	464 mm


Table 2/2

Catalog Number	Hole Size (HS)	Unit Weight
T416C	70 mm	7.3 kg

ADDITIONAL PRODUCT DETAILS

T416CKEY sold sperately

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE