

# BS-125A Four Pole Insulating Support



## CERTIFICATIONS



## FEATURES

Create custom four pole distribution blocks for an electrical distribution system

Protection screen can be attached directly to the support

Includes screws to mount threaded copper busbars

Clips on to DIN rail using DR-CLIP or mounts with screws

Halogen free

RoHS compliant

## SPECIFICATIONS

Table 1/3

| Catalog Number | Article Number | Material                                | Finish            | Max Working Voltage, IEC (Ui) | Working Temperature | Typical Application Current Rating |
|----------------|----------------|-----------------------------------------|-------------------|-------------------------------|---------------------|------------------------------------|
| BS-125A        | 551311         | Steel, Glass Fibre Reinforced Polyamide | Electrogalvanized | 1000, 1500                    | -40 to 130 °C       | 125 - 160 A                        |

Table 2/3

| Catalog Number | Article Number | Complies With                                                             | Flammability Rating | Busbar Width | Busbar Thickness | Depth (D) |
|----------------|----------------|---------------------------------------------------------------------------|---------------------|--------------|------------------|-----------|
| BS-125A        | 551311         | IEC® 60439.1,<br>IEC® 61439.1,<br>IEC® 60695-2-11 (Glow Wire Test 960 °C) | UL® 94V-0           | 12 - 15 mm   | 4 - 5 mm         | 117.5mm   |


Table 3/3

| Catalog Number | Article Number | Height (H) | Screw Diameter (Sc) | Unit Weight |
|----------------|----------------|------------|---------------------|-------------|
| BS-125A        | 551311         | 126 mm     | 5                   | 0.1 kg      |

## ADDITIONAL PRODUCT DETAILS

Must be used with copper busbars.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**