

# 19" Front Panel, Plastic



19" plastic made clip on Front Panels with esthetic design are specially made for the datacom vertical. The easy clip on panels help in air flow management and also simultaneously providing an appealing look for the network rack.

## CERTIFICATIONS



## FEATURES

Attractive design

Simple fitting by clipping onto the 19" plane

## SPECIFICATIONS

**Accessory Type:** Front panel

Table 1/3

| Catalog Number | Type            | Mounting   | EMC Shielding | Material | Front Finish | Rear Finish |
|----------------|-----------------|------------|---------------|----------|--------------|-------------|
| 87927-991      | 19" Front Panel | Snapped in | No            | ABS      | Raw          | Raw         |
| 87927-992      | 19" Front Panel | Snapped in | No            | ABS      | Raw          | Raw         |
| 23130-623      | 19" Front Panel | Snapped in | No            | ABS      |              |             |
| 23130-622      | 19" Front Panel | Snapped in | No            | ABS      |              |             |

Table 2/3

| Catalog Number | Color Code | Rack Height | Height  | Rack Width | Width | Depth |
|----------------|------------|-------------|---------|------------|-------|-------|
| 87927-991      | RAL 7035   | 1U          | 43.71mm | 95HP       | 482mm | 12mm  |
| 87927-992      | RAL 7035   | 2U          | 88.17mm | 95HP       | 482mm | 12mm  |
| 23130-623      | RAL 7035   | 6U          | 266.6mm | 95HP       | 483mm | 2mm   |
| 23130-622      | RAL 9005   | 6U          | 266.6mm | 95HP       | 483mm | 2mm   |

Table 3/3

| Catalog Number | Package Quantity | Quick Ship |
|----------------|------------------|------------|
| 87927-991      | 10               | No         |
| 87927-992      | 10               | No         |
| 23130-623      | 10               | No         |
| 23130-622      | 10               | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**