

# Front Panel, Unshielded, With Fastener Pin

## Power Utilities



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

## CERTIFICATIONS



## FEATURES

Enable grounding of the front area (protection class 1)

## SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish | Treated Edges |
|----------------|------------|------------------|----------------|--------------|-------------|---------------|
| 20119-159      | 7 HP       | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-160      | 14 HP      | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-161      | 21 HP      | 1                | Screw-on Front | Anodized     | Conductive  | No            |
| 20119-162      | 28 HP      | 1                | Screw-on Front | Anodized     | Conductive  | No            |

| CatalogNumber | Rack Width | Package Quantity | Mounting       | Front Finish | Rear Finish | Treated Edges |
|---------------|------------|------------------|----------------|--------------|-------------|---------------|
| 20119-163     | 42 HP      | 1                | Screw-on Front | Anodized     | Anodized    | No            |

Table 2/3

| Catalog Number | Complies With                   | EMC Shielding | Height   | Material | Product Type | Rack Height |
|----------------|---------------------------------|---------------|----------|----------|--------------|-------------|
| 20119-159      | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  | 3 U         |
| 20119-160      | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  | 3 U         |
| 20119-161      | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  | 3 U         |
| 20119-162      | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  | 3 U         |
| 20119-163      | IEC 60297-3-101, IEEE 1101.1/10 | No            | 128.4 mm | Aluminum | Front Panel  | 3 U         |

Table 3/3

| Catalog Number | Type                       | Width    |
|----------------|----------------------------|----------|
| 20119-159      | Front Panel without Handle | 35.2 mm  |
| 20119-160      | Front Panel without Handle | 70.8 mm  |
| 20119-161      | Front Panel without Handle | 106.3 mm |
| 20119-162      | Front Panel without Handle | 141.9 mm |
| 20119-163      | Front Panel without Handle | 213 mm   |

## ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**