nVent SCHROFF

We connect and protect

Socket Strip, SCHUKO/UTE, Local Display, 6 x SCHUKO/UTE Outlets

CATALOG NUMBER

60110-294







PDU with local power meter. Relevant Power data are shown on an integrated display.

CERTIFICATIONS

RoHS COMPLIANT

EAC

FEATURES

- Integrated measurement and display via local display unit
- Socket strips with Schuko sockets
- Mounting height 1 U
- Socket strips can be rotated through all four directions (in 90° increments) during installation

Horizontal and vertical mounting

Measurement functions: Voltage, Current, Power, Frequency, cos phi

PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: SCHUKO

Socket Quantity: 6

Color: Grey

Switched Outlets: No

Length: 438.5mm

Voltage AC: 230V

Depth: 44mm

Finish: Anodized

Gross Weight: 0.886kg

Material: Aluminum; Polyamide

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.