

# nVent CADDY Speed Link Light Pack with Wedge Anchor



The nVent CADDY Speed Link Light Pack with Wedge Anchor includes a precut length (1m and 2m) of 1mm wire rope riveted to a wedge anchor together with an ultra-low-profile locking device. Contractors can quickly and safely install it to the concrete ceiling to support and secure lighting and signage.

## FEATURES

Complete system includes wire, locking device and wedge anchor from fischerwerke GmbH &Co. KG

Quickly and easily attaches into cracked and non-cracked concrete

No special tools required

ETA 06/0175 approval available from fischerwerke GmbH &Co. KG

## SPECIFICATIONS

**Static Load Safety Factor:** 5:1  
**Material:** Steel;Brass  
**Finish:** Electrogalvanized

Table 1/2

| Catalog Number | Article Number | Wire Rope Diameter | Wire Rope Length | Length (L) | Height (H) | Width (W) |
|----------------|----------------|--------------------|------------------|------------|------------|-----------|
| CLP1L1WA6      | 196093         | 1 mm               | 1m               | 54mm       | 17 mm      | 12.5 mm   |
| CLP1L2WA6      | 196094         | 1 mm               | 2m               | 54mm       | 17 mm      | 12.5 mm   |


Table 2/2

| Catalog Number | Article Number | Thickness (T) | Angle (a) | Static Load |
|----------------|----------------|---------------|-----------|-------------|
|----------------|----------------|---------------|-----------|-------------|

|           |        |        |      |      |
|-----------|--------|--------|------|------|
| CLP1L1WA6 | 196093 | 6.5 mm | 60 ° | 100N |
| CLP1L2WA6 | 196094 | 6.5 mm | 60 ° | 100N |

**Drill Bit Diameter:** 6mm  
**Drill Hole Depth:** 31mm  
**Embedment Depth:** 25 mm Min

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**

