We connect and protect

VKR Trapezoidal Deck Hanger

FEATURES

Supports threaded rod

SPECIFICATIONS

Finish: nVent CADDY Armour

Material: Spring Steel

Table 1/2

Catalog Number	Article Number	Rod Size (RS)	Flange Thickness (FT)	Hole Size (HS)	Diameter (Ø)	Static Load 1 (F1)
M8VKR	160650	8	0.8 - 3 mm	7 mm	7 mm	450N
M10VKR	160660	10	0.8 - 3 mm	7 mm	7 mm	450N
M6VKR	160640	6	0.8 - 3 mm	7 mm	7 mm	450N

Table 2/2

Catalog Number	Article Number	Static Load 2 (F2)
M8VKR	160650	900N
M10VKR	160660	900N

Catalog Number	Article Number	Static Load 2 (F2)
M6VKR	160640	600N

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 0.8 - 2.0 mm flange thickness. Static Load 2 represents 2.0 - 3.0 mm flange thickness.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

Our powerful portfolio of brands:
CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.