

# Plug-In Unit U-Profile Front Panel for XL Handle

Front panel for XL handle. Shieldable with textile gasket. with or without cutout for a microswitch.



## CERTIFICATIONS



## FEATURES

Al, front anodized, sides and rear conductive

Suitable for sleeve and collar screw

U-front profile, shieldable, for inserter/extractor handle, type XL

## SPECIFICATIONS

|                        |                              |
|------------------------|------------------------------|
| <b>Material:</b>       | Aluminum                     |
| <b>Finish:</b>         | Anodized; Passivated         |
| <b>Accessory Type:</b> | Front panel                  |
| <b>Product Type:</b>   | Front Panel                  |
| <b>Type:</b>           | Front Panel for Handle (PIU) |
| <b>EMC Shielding:</b>  | No (Retrofittable)           |

Table 1/3

| Catalog Number | Rack Width | Package Quantity | Handle Type | Mounting       | Gasket Type | Front Finish |
|----------------|------------|------------------|-------------|----------------|-------------|--------------|
| 30849-153      | 4HP        | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |

| CatalogNumber | Rack Width | Package Quantity | Handle Type | Mounting       | Gasket Type | Front Finish |
|---------------|------------|------------------|-------------|----------------|-------------|--------------|
| 30849-154     | 4HP        | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |
| 30849-156     | 8HP        | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |
| 30849-155     | 8HP        | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |
| 30849-158     | 12HP       | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |
| 30849-157     | 12HP       | 1                | XL          | Screw-on Front | Textile EMC | Anodized     |

Table 2/3

| Catalog Number | Rear Finish | Treated Edges | Complies With                   | Depth (D) | Height (H) | Rack Height |
|----------------|-------------|---------------|---------------------------------|-----------|------------|-------------|
| 30849-153      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |
| 30849-154      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |
| 30849-156      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |
| 30849-155      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |
| 30849-158      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |
| 30849-157      | Conductive  | No            | IEC 60297-3-101, IEEE 1101.1/11 | 2.5mm     | 261.8mm    | 6U          |

Table 3/3

| Catalog Number | Width (W) | Quick Ship |
|----------------|-----------|------------|
| 30849-153      | 20mm      | No         |
| 30849-154      | 20mm      | No         |
| 30849-156      | 40.3mm    | No         |



### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**