

## Drawing Desks, DDK



This drawing desk provides a stable surface and can be used as a temporary working desk, for documents, a computer, or measuring devices. The desk folds away flush with the frame, and the angle can be adjusted.

### FEATURES

---

Description: Mounted directly to the door frame it provides a solid surface for documents, computer or measuring devices. The desk can be easily folded and locked within the door frame space. An automatic safety positioning system locks the desk at angles of 55°, 70° and 90°. The DDK800R5 can also be mounted on a 1000 mm wide door, by the use of the DCP1002 accessory.

Material: 1.35 mm mild steel.

Finish: RAL 7035 structured powder coating.

Pack quantity: 1 piece with mounting accessories.

SPECIFICATIONS

**Thickness:** 1.35mm  
**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

| Table 1/1      |                |        |       |       |                    |                |
|----------------|----------------|--------|-------|-------|--------------------|----------------|
| Catalog Number | Article Number | Height | Width | Depth | Enclosure Material | Product Family |
| DDK600R5       | DDK600R5       | 342mm  | 487mm | 365mm | Mild Steel         | Free-Standing  |
| DDK800R5       | DDK800R5       | 342mm  | 687mm | 365mm | Mild Steel         | Free-Standing  |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE