

Early Streamer Emission Terminal



nVent ERICO INTERCEPTOR ESE i-Series generates controlled magnitude and frequency pulses at the tip of the terminal during high static fields prior to a lightning discharge. This enables the creation of an upward leader from the terminal that propagates toward the downward leader coming from the thunder cloud.

These early streamer emission air terminals (ESEAT) are in accordance with the 2011 edition of NFC 17-102. The design requirements, protection level calculations and protection radius are obtained from this standard. Due to the internal control circuit, the nVent ERICO INTERCEPTOR ESE i-Series enables the early launching of an upward leader compared to other passive components.

The nVent ERICO INTERCEPTOR ESE i-Series has been extensively tested at an independent high-voltage laboratory in accordance with the revised 2011 requirements of French NFC 17-102. The testing, as defined in the standard, was designed to simulate naturally occurring conditions and allow comparison of the performance between differing types of lightning protection systems.

CERTIFICATIONS



FEATURES

Designed and tested to NF C 17-102 and similar standards

Available in three models to suit specific site requirements

Suitable for use with a variety of downconductor systems including tape, stranded conductor and nVent ERICO Ericore conductor

SPECIFICATIONS

Complies With: NF C17-102:2011;NP 4426:2013;UNE 21186:2011

Table 1/2						
Catalog Number	Material	Triggered Advance, ΔT	Temperature	Diameter ($\varnothing$)	Height (H)	Thread Size (TS)
SI25I	Stainless Steel 304L (EN 1.4306)	25 μ s	120 °C Max	28 mm	684.6 mm	MF25
SI60I	Stainless Steel 304L (EN 1.4306)	60 μ s	120 °C Max	28 mm	684.6 mm	MF25
SI60I316	Stainless Steel 316L (EN 1.4404)	60 μ s	120 °C Max	28 mm	684.6 mm	MF25
SI45I	Stainless Steel 304L (EN 1.4306)	45 μ s	120 °C Max	28 mm	684.6 mm	MF25

Table 2/2		
Catalog Number	Unit Weight	Certifications
SI25I	1.53 kg	UL (NF C17-102)
SI60I	1.45 kg	UL (NF C17-102)
SI60I316	1.45 kg	
SI45I	1.36 kg	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE