

# P13 Position Coupler, Male and Nut Only, Worldwide Design

Used in segmental pour and closure pour applications. Male and female components are sold separately.



## FEATURES

Designed to splice two curved, bent or straight bars, when neither bar can be rotated and where the ongoing bar is NOT free to move in its axial direction

Adjustability in the female end of the coupler allows the coupler to extend out to meet the taper-threaded reinforcing bar

## SPECIFICATIONS

**Finish:** Plain  
**Coupler Adjustment:** Standard  
**Material:** Steel

Table 1/2

| Catalog Number | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | A     |
|----------------|--------------------|----------------|--------------------|--------------|------------|-------|
| EL10P13LMN     | 10 mm              | #3             |                    | 20 mm        | 95mm       | 50 mm |
| EL12P13LMN     | 12 mm              | #4             | 10M                | 20 mm        | 99mm       | 49 mm |
| EL14P13LMN     | 14 mm              |                |                    | 20 mm        | 106mm      | 52 mm |
| EL16P13LMN     | 16 mm              | #5             | 15M                | 25 mm        | 113mm      | 55 mm |

| CatalogNumber | Rebar Size, Metric | Rebar Size, US | Rebar Size, Canada | Diameter (Ø) | Length (L) | A      |
|---------------|--------------------|----------------|--------------------|--------------|------------|--------|
| EL18P13LMN    | 18 mm              |                |                    | 25 mm        | 125mm      | 61 mm  |
| EL20P13LMN    | 20 mm              | #6             | 20M                | 30 mm        | 155mm      | 73 mm  |
| EL22P13LMN    | 22 mm              | #7             |                    | 35 mm        | 164mm      | 78 mm  |
| EL25P13LMN    | 25 mm              | #8             | 25M                | 35 mm        | 172mm      | 81 mm  |
| EL28P13LMN    | 28 mm              | #9             | 30M                | 40 mm        | 178mm      | 82 mm  |
| EL32P13LMN    | 32 mm              | #10            |                    | 45 mm        | 195mm      | 93 mm  |
| EL36P13LMN    | 36 mm              | #11            | 35M                | 50 mm        | 210mm      | 99 mm  |
| EL40P13LMN    | 40 mm              |                |                    | 55 mm        | 224mm      | 106 mm |

Table 2/2


| Catalog Number | Bar Depth (BD) | Thread Size (TS) | Unit Weight |
|----------------|----------------|------------------|-------------|
| EL10P13LMN     | 18mm           | M18              | 0.21 kg     |
| EL12P13LMN     | 19mm           | M18              | 0.21 kg     |
| EL14P13LMN     | 21mm           | M18              | 0.21 kg     |
| EL16P13LMN     | 24mm           | M22              | 0.34 kg     |
| EL18P13LMN     | 29mm           | M24              | 0.43 kg     |
| EL20P13LMN     | 35mm           | M26              | 0.64 kg     |
| EL22P13LMN     | 37mm           | M31              | 0.96 kg     |
| EL25P13LMN     | 40mm           | M34              | 1.11 kg     |
| EL28P13LMN     | 42mm           | M37              | 1.42 kg     |

| Catalog Number | Bar Depth (BD) | Thread Size (TS) | Unit Weight |
|----------------|----------------|------------------|-------------|
| EL32P13LMN     | 45mm           | M42              | 2.07 kg     |
| EL36P13LMN     | 52mm           | M46              | 2.65 kg     |
| EL40P13LMN     | 57mm           | M53              | 3.55 kg     |

## ADDITIONAL PRODUCT DETAILS

Bar dimensions and weights listed may vary by region. Coupler sizes not shown may be available by special order. Contact your nVent LENTON representative for more information.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**