



# Horizontal Rail, Front, Type H-LD, Heavy, Long Lip, for IEEE Application, 1000 mm

**CATALOG NUMBER**

**34560-301**



## Combinations of horizontal rails and side panels

|                 |                                                                                     | + "can be combined." |                                   | + "combination not recommended"   |                                   |
|-----------------|-------------------------------------------------------------------------------------|----------------------|-----------------------------------|-----------------------------------|-----------------------------------|
| Support # 8     |    | -                    | reference to double<br>side panel | reference to double<br>side panel | reference to double<br>side panel |
|                 |    | +                    | +                                 | +                                 | +                                 |
| Support # 1     |    | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
|                 |    | +                    | +                                 | +                                 | +                                 |
| Horizontal rail |    | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
|                 |    | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
| Side panel      |  | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
|                 |  | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
| Support # 1     |  | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |
|                 |  | +                    | reference to double<br>side panel | reference to double<br>side panel | +                                 |

Only panel 1000

The horizontal rail with a long lip enables the use of IEEE insertion / extraction handles.

## CERTIFICATIONS



## FEATURES

For plug-in units with IEEE handle

Long lip (H-LD)

### Installation at top and bottom

For CPCI and VME64x systems

Aluminum extrusion, anodized finish, conductive contact surface

## PRODUCT ATTRIBUTES

Rack Width: 195HP

Package Quantity: 1

Finish: Anodized

Length: 1000mm

Material: Aluminum

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Horizontal Rail

Type: Heavy, LD

Works With: Subracks; Cases

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**