

Stainless Steel Ground Rod, Sectional Internal Thread



FEATURES

Stainless steel sectional ground rod with internal threading

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Tensile Strength	Ground Rod Diameter, Actual (Ø)	Thread Size (TS)	Length (L)
SSR16	710010	Stainless Steel 316 (EN 1.4401)	483 kPa Min	16 mm	M10	1.2mm

Table 2/2

Catalog Number	Article Number	Unit Weight
SSR16	710010	1.8 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE