nVent | HOFFMAN

We connect and protect

# Vertical Dividing Bars for 1-Door, VB, 2000x90x24mm, Plated, Mild Steel

## CATALOG NUMBER

**VB2000**

The dividing vertical bar increases the mounting possibilities available within the enclosure and divides it into two useable spaces.

## FEATURES

Description: Fitted in the centre of 1200 mm or 1600 mm wide enclosures (front and rear) to provide standard mounting facilities in two vertical sections of 600 mm or 800 mm. This enables separate fitting of equipment such as swing frames, system profiles, in either section of the enclosure.

Material: 1.75 mm zinc plated steel.

Pack quantity: 1 pair without mounting accessories.

Mounting requirements: Add VBK for mounting. For complete mounting facilities in the division add VBD.

## PRODUCT ATTRIBUTES

Height: 2000mm

Width: 89mm

Depth: 24mm

Enclosure: Single door

Material: Steel

Finish: Plated

Thickness: 1.75mm

Enclosure Material: Mild Steel

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.