

# Partial Doors For Floor Standing Enclosures, DP



Partial doors allow for many different, easily accessible configurations of separate compartments, within the enclosure.

## FEATURES

Description: To divide the enclosure front into sections when used in conjunction with the horizontal divider CDH/CHDK. Equipped with double-bit 3 mm lock (1 lock up to 400 mm, over 400 mm height 2 locks).

Material: 1.75 mm steel plate.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 44.

Pack quantity: 1 door with hinges, locks and mounting accessories.

Mounting requirements: Add CDH for MC frames and use CDHK for MK frames. Use DPC/DPCV for top and bottom panels.

## SPECIFICATIONS

**Color:** Light Gray  
**Material:** Mild Steel  
**Finish:** Powder Coated  
**Color Code:** RAL 7035

Table 1/1

Catalog Number	Height	Width	Depth	Enclosure Material	Product Family	Quick Ship
DP01504R5	150mm	400mm	17mm	Mild Steel	Free-Standing	No
DP01506R5	150mm	600mm	17mm	Mild Steel	Free-Standing	No
DP01508R5	150mm	800mm	17mm	Mild Steel	Free-Standing	No
DP02004R5	200mm	400mm	17mm	Mild Steel	Free-Standing	No
DP02006R5	200mm	600mm	17mm	Mild Steel	Free-Standing	No
DP02008R5	200mm	800mm	17mm	Mild Steel	Free-Standing	No
DP02504R5	250mm	400mm	17mm	Mild Steel	Free-Standing	No
DP02506R5	250mm	600mm	17mm	Mild Steel	Free-Standing	No
DP02508R5	250mm	800mm	17mm	Mild Steel	Free-Standing	No
DP03004R5	300mm	400mm	17mm	Mild Steel	Free-Standing	No
DP03006R5	300mm	600mm	17mm	Mild Steel	Free-Standing	No
DP03008R5	300mm	800mm	17mm	Mild Steel	Free-Standing	No
DP04004R5	400mm	400mm	17mm	Mild Steel	Free-Standing	No
DP04006R5	400mm	600mm	17mm	Mild Steel	Free-Standing	No
DP04008R5	400mm	800mm	17mm	Mild Steel	Free-Standing	No
DP05004R5	500mm	400mm	17mm	Mild Steel	Free-Standing	No

Catalog Number	Height	Width	Depth	EnclosureMaterial	Product Family	Quick Ship
DP05006R5	500mm	600mm	17mm	Mild Steel	Free-Standing	No
DP05008R5	500mm	800mm	17mm	Mild Steel	Free-Standing	No
DP06004R5	600mm	400mm	17mm	Mild Steel	Free-Standing	No
DP06006R5	600mm	600mm	17mm	Mild Steel	Free-Standing	No
DP06008R5	600mm	800mm	17mm	Mild Steel	Free-Standing	No
DP08006R5	800mm	600mm	17mm	Mild Steel	Free-Standing	No
DP08008R5	800mm	800mm	17mm	Mild Steel	Free-Standing	No
DP10006R5	1000mm	600mm	17mm	Mild Steel	Free-Standing	No
DP10008R5	1000mm	800mm	17mm	Mild Steel	Free-Standing	No
DP12006R5	1200mm	600mm	17mm	Mild Steel	Free-Standing	No
DP12008R5	1200mm	800mm	17mm	Mild Steel	Free-Standing	No

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**