

# Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

## Power Utilities

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

### FEATURES

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

### SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Complies With
21630-876	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-877	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-878	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-879	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-880	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-881	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-882	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Complies With
21630-883	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Catalog Number	Locking Type	Material	Product Type	Protection Rating	Type	Works With
21630-876	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-877	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-878	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-879	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-880	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-881	4-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-882	5-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-883	5-Point Locking	Steel	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**