

Varistar CP Steel Door, Perforated With Multi-Point Locking

Power Utilities

EMC doors with good contact with the frame and gasket to achieve high attenuation.

The 4 point locking helps achieve necessary contact to avoid EMI effects on electronics.

FEATURES

Perforated door with 4-point locking for EMC applications

Interior galvanized

Opening angle 180°

Lever handle with push button

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-533	24 U	1200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-534	24 U	1200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-535	29 U	1400 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-536	29 U	1400 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-537	33 U	1600 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-538	33 U	1600 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-539	38 U	1800 mm	600 mm	Black Grey	RAL 7021	4-Point Locking

CatalogNumber	Rack Height	Height	Width	Color	Color Code	Locking Type
21630-540	38 U	1800 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-541	42 U	2000 mm	600 mm	Black Grey	RAL 7021	4-Point Locking
21630-542	42 U	2000 mm	800 mm	Black Grey	RAL 7021	4-Point Locking
21630-543	47 U	2200 mm	600 mm	Black Grey	RAL 7021	5-Point Locking
21630-544	47 U	2200 mm	800 mm	Black Grey	RAL 7021	5-Point Locking

Table 2/2

Catalog Number	Material	Product Type	Type
21630-533	Steel	Cabinet Door	Steel Door, Perforated
21630-534	Steel	Cabinet Door	Steel Door, Perforated
21630-535	Steel	Cabinet Door	Steel Door, Perforated
21630-536	Steel	Cabinet Door	Steel Door, Perforated
21630-537	Steel	Cabinet Door	Steel Door, Perforated
21630-538	Steel	Cabinet Door	Steel Door, Perforated
21630-539	Steel	Cabinet Door	Steel Door, Perforated
21630-540	Steel	Cabinet Door	Steel Door, Perforated
21630-541	Steel	Cabinet Door	Steel Door, Perforated
21630-542	Steel	Cabinet Door	Steel Door, Perforated
21630-543	Steel	Cabinet Door	Steel Door, Perforated
21630-544	Steel	Cabinet Door	Steel Door, Perforated

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE