nVent | SCHROFF

We connect and protect

Strap Handle Universal, 22 or 25 mm

The universal strap handle can be assembled to the side panel of cases.

CERTIFICATIONS

RoHS COMPLIANT

FEATURES

Static load-carrying capacity 20 kg

SPECIFICATIONS

Works With: Cases

Product Family: RatiopacPRO; RatiopacPRO AIR; PropacPRO; CompacPRO; Comptec

Product Type: Handle

Table 1/1

Catalog Number	Length	Package Quantity	Handle Type	Color	Width	Quick Ship
10504-002	170mm	1	Strap	Black	22mm	No
10504-003	240mm	1	Strap	Black	22mm	No
20850-249	230mm	1	Strap	Grey	25mm	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe
Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia
Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India
Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.