

# Telescopic Slide, Universal, Heavy Load, 2 U



Telescopic slides with 10 to 100 kg load capacity, > 100% extension length and with lateral mounting capability on 19". Robust telescopic sliding-rails - suitable for the installation of 19 inch chassis are suitable for mounting server enclosures from our product portfolio. Due to the extremely robust construction and high load capacity, the telescopic slides can also be used with very heavy housings.

## CERTIFICATIONS



## FEATURES

Static load-carrying capacity per pair 72 - 100 kg

Lateral mounting on the 19" uprights (19" plane remains free for fixing the extension/drawer)

End stop damped

Extension length > 100 %

Rail width k = 19.1 mm, max. installation width of extension/drawer w = 411 mm

## SPECIFICATIONS

**Material:** Steel  
**Product Type:** Telescopic Slide  
**Finish:** Zinc Plated

Table 1/1

| Catalog Number | Length | Package Quantity | Static Load | Type      | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-190      | 300mm  | 2                | 77kg        | Universal | No         |

| Catalog Number | Length | Package Quantity | Static Load | Type      | Quick Ship |
|----------------|--------|------------------|-------------|-----------|------------|
| 20110-198      | 700mm  | 2                | 72kg        | Universal | No         |
| 20110-196      | 600mm  | 2                | 88kg        | Universal | No         |
| 20110-195      | 550mm  | 2                | 94kg        | Universal | No         |
| 20110-194      | 500mm  | 2                | 100kg       | Universal | No         |
| 20110-191      | 350mm  | 2                | 83kg        | Universal | No         |
| 20110-193      | 450mm  | 2                | 94kg        | Universal | No         |
| 20110-192      | 400mm  | 2                | 88kg        | Universal | No         |

## ADDITIONAL PRODUCT DETAILS

To mount on 19" plane please order assembly kit separately.

Universal telescopic rails can also be fitted without additional components in non-standard applications, thus also in other than 19" cabinets.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**