

Varistar CP Cabinet Frame, Seismic



Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FEATURES

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFICATIONS

Dynamic Load:	250kg
Static Load:	1600kg
Product Type:	Cabinet/Rack Frame
Frame Material:	Steel

Table 1/3

Catalog Number	Rack Height	Height	Width	Depth	Package Quantity	Shock and Vibration Tolerance
20630-358	33U	1600mm	600mm	600mm	1	5g (force)
20630-359	33U	1600mm	600mm	600mm	1	5g (force)
20630-360	33U	1600mm	800mm	600mm	1	5g (force)
20630-361	33U	1600mm	800mm	800mm	1	5g (force)

CatalogNumber	Rack Height	Height	Width	Depth	Package Quantity	Shock and Vibration Tolerance
20630-362	38U	1800mm	600mm	600mm	1	5g (force)
20630-363	38U	1800mm	600mm	800mm	1	5g (force)
20630-364	38U	1800mm	800mm	600mm	1	5g (force)
20630-365	38U	1800mm	800mm	800mm	1	5g (force)
20630-366	42U	2000mm	600mm	600mm	1	5g (force)
20630-367	42U	2000mm	600mm	800mm	1	5g (force)
20630-370	42U	2000mm	800mm	600mm	1	5g (force)
20630-371	42U	2000mm	800mm	800mm	1	5g (force)
20630-374	47U	2200mm	600mm	600mm	1	5g (force)
20630-375	47U	2200mm	600mm	800mm	1	5g (force)
20630-376	47U	2200mm	800mm	600mm	1	5g (force)
20630-377	47U	2200mm	800mm	800mm	1	5g (force)
20630-368	42U	2000mm	600mm	1000mm	1	5g (force)
20630-369	42U	2000mm	600mm	1200mm	1	5g (force)
20630-372	42U	2000mm	800mm	1000mm	1	5g (force)
20630-373	42U	2000mm	800mm	1200mm	1	5g (force)

Table 2/3

Catalog Number	Frequency	Color	Color Code	Complies With	Finish	Material
----------------	-----------	-------	------------	---------------	--------	----------

20630-358	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-359	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-360	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-361	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-362	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-363	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-364	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-365	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-366	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-367	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-370	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-371	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-374	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-375	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-376	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-377	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-368	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-369	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
20630-372	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel

20630-373	50 Hz	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2	Powder Coated	Steel
-----------	-------	------------	----------	-----------------------------	---------------	-------

Table 3/3

Catalog Number	Type	Works With	Quick Ship
20630-358	Seismic	Varistar CP	No
20630-359	Seismic	Varistar CP	No
20630-360	Seismic	Varistar CP	No
20630-361	Seismic	Varistar CP	No
20630-362	Seismic	Varistar CP	No
20630-363	Seismic	Varistar CP	No
20630-364	Seismic	Varistar CP	No
20630-365	Seismic	Varistar CP	No
20630-366	Seismic	Varistar CP	No
20630-367	Seismic	Varistar CP	No
20630-370	Seismic	Varistar CP	No
20630-371	Seismic	Varistar CP	No
20630-374	Seismic	Varistar CP	No
20630-375	Seismic	Varistar CP	No
20630-376	Seismic	Varistar CP	No
20630-377	Seismic	Varistar CP	No
20630-368	Seismic	Varistar CP	No

Catalog Number	Type	Works With	Quick Ship
20630-369	Seismic	Varistar CP	No
20630-372	Seismic	Varistar CP	No
20630-373	Seismic	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE