

# Varistar CP Deco Frame



## FEATURES

19" plane is integrated into decorative frame

Aluminum, decorative frame for open cabinet

Open at front, no door can be fitted

## SPECIFICATIONS

**Material:** Aluminum  
**Product Type:** Cabinet/Rack Frame  
**Protection Rating:** IP20

Table 1/2

| Catalog Number | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|----------------|-------------|--------|-------|------------------|------------|------------|
| 21630-309      | 24U         | 1200mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-310      | 29U         | 1400mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-311      | 33U         | 1600mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-312      | 38U         | 1800mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-313      | 42U         | 2000mm | 600mm | 1                | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|---------------|-------------|--------|-------|------------------|------------|------------|
| 21630-314     | 47U         | 2200mm | 600mm | 1                | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Finish        | Frame Material | Type       | Works With  | Quick Ship |
|----------------|---------------|----------------|------------|-------------|------------|
| 21630-309      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |
| 21630-310      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |
| 21630-311      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |
| 21630-312      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |
| 21630-313      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |
| 21630-314      | Powder Coated | Steel          | Deco Frame | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**