

# Varistar CP Steel Door, Perforated With 3-Point Electronic Locking



Varistar CP perforated steel door 3-point locking for IP 20 applications.

## FEATURES

Perforated steel door with 3-point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

## SPECIFICATIONS

**Locking Type:** 3-Point Locking, Electronic

**Product Type:** Cabinet Door

**Protection Rating:** IP20

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Type                                 | Package Quantity | Color      |
|----------------|-------------|--------|-------|--------------------------------------|------------------|------------|
| 21630-814      | 42U         | 2000mm | 600mm | Steel Door, Perforated, Hinged, Left | 1                | Black Grey |
| 21630-815      | 47U         | 2200mm | 600mm | Steel Door, Perforated, Hinged, Left | 1                | Black Grey |
| 21630-816      | 52U         | 2450mm | 600mm | Steel Door, Perforated, Hinged, Left | 1                | Black Grey |

| CatalogNumber | Rack Height | Height | Width | Type                                        | Package Quantity | Color      |
|---------------|-------------|--------|-------|---------------------------------------------|------------------|------------|
| 21630-817     | 42U         | 2000mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Left  | 1                | Black Grey |
| 21630-818     | 47U         | 2200mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Left  | 1                | Black Grey |
| 21630-819     | 52U         | 2450mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Left  | 1                | Black Grey |
| 21630-895     | 42U         | 2000mm | 600mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |
| 21630-896     | 47U         | 2200mm | 600mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |
| 21630-897     | 52U         | 2450mm | 600mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |
| 21630-898     | 42U         | 2000mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |
| 21630-899     | 42U         | 2000mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |
| 21630-900     | 52U         | 2450mm | 800mm | Steel Door,<br>Perforated,<br>Hinged, Right | 1                | Black Grey |

Table 2/2

| Catalog Number | Color Code | Complies With | Finish        | Works With  | Quick Ship |
|----------------|------------|---------------|---------------|-------------|------------|
| 21630-814      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-815      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-816      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-817      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-818      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |

| Catalog Number | Color Code | Complies With | Finish        | Works With  | Quick Ship |
|----------------|------------|---------------|---------------|-------------|------------|
| 21630-819      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-895      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-896      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-897      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-898      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-899      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |
| 21630-900      | RAL 7021   | IEC 61587-1   | Powder Coated | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**