

# nVent CADDY Speed Link SLK with Y-Toggle



#### **CERTIFICATIONS**





## **FEATURES**

Complete system includes wire, locking device and two pre-assembled toggle end fittings

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

## **SPECIFICATIONS**

Wire Rope Diameter: 1.5 mm Static Load Safety Factor: 5:1

Finish: Electrogalvanized

Material: Steel;Zinc Alloy;Polypropylene


Complies With: SMACNA HVAC-DCS


Table 1/1								
Catalog Number	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	В	Static Load		
SLK15Y300L3R 2	196648	3m	0.3m	39 mm	5 mm	195N		


CatalogNumber	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	В	Static Load
SLK15Y500L3	196528	3m	0.5m	39 mm	5 mm	195N


Thickness (T): 12.5 mm
Width (W): 19 mm
Height (H): 55 mm
Angle (a): 90 ° Max

#### **DIAGRAMS**









#### **WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### **North America**

+1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support

# Europe

Netherlands: +31 800-0200135 France:

+33 800 901 793

#### Europe

Germany: 800 1890272 Other Countries: +31 13 5835404

# APAC

Shanghai: + 86 21 2412 1618/19 Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:

CADDY

**ERICO** 

**HOFFMAN** 

ILSCO SCHROFF

TRACHTE



©2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.