

Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 1000 mm

CATALOG NUMBER

34566-301



Combinations of horizontal rails and side panels

$\oplus$ = can be combined, $\oplus$ = combination not recommended

RAILTYPE #		1	2	3	4
RAILTYPE 1		-	side rail $\oplus$ Plus side rail $\oplus$ Plus	side rail $\oplus$ Plus side rail $\oplus$ Plus	side rail $\oplus$ Plus side rail $\oplus$ Plus
RAILTYPE 2		+	side rail $\oplus$ Plus side rail $\oplus$ Plus	side rail $\oplus$ Plus side rail $\oplus$ Plus	+
RAILTYPE 3		side rail $\oplus$ Plus side rail $\oplus$ Plus	side rail $\oplus$ Plus side rail $\oplus$ Plus	-	-
RAILTYPE 4		side panel	side panel	side panel	side panel

1)TYPE 1 2)TYPE 2 3)TYPE 3 4)TYPE 4

side panel side panel side panel side panel

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

CERTIFICATIONS



FEATURES

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Rack Width: 195HP

Package Quantity: 1

Finish: Anodized

Length: 1000mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Net Weight: 0.6kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE