


# Varistar CP Seismic Base Plate, EMC, with Cable Entry, One-Piece

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.



## FEATURES

Installation from outside

Cutout at rear

60 mm deep

Cable ducting with IP 55 / EMC gasket

## SPECIFICATIONS

**Product Type:** Cabinet/Rack Base

**Finish:** Hot-Dip Galvanized

**Material:** Steel

Table 1/2

| Catalog Number | Width | Depth  | Package Quantity | Complies With                               | Type                       | Works With  |
|----------------|-------|--------|------------------|---------------------------------------------|----------------------------|-------------|
| 20630-317      | 600mm | 600mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-318      | 600mm | 800mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-319      | 600mm | 1000mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |

| CatalogNumber | Width  | Depth  | Package Quantity | Complies With                               | Type                       | Works With  |
|---------------|--------|--------|------------------|---------------------------------------------|----------------------------|-------------|
| 20630-320     | 600mm  | 1200mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-321     | 600mm  | 600mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-322     | 800mm  | 800mm  | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-323     | 1000mm | 1000mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |
| 20630-324     | 800mm  | 1200mm | 1                | IEC 61587-1,<br>IEC 61587-2,<br>IEC 61587-3 | Base Plate,<br>Cable Entry | Varistar CP |

Table 2/2

| Catalog Number | Quick Ship |
|----------------|------------|
| 20630-317      | No         |
| 20630-318      | No         |
| 20630-319      | No         |
| 20630-320      | No         |
| 20630-321      | No         |
| 20630-322      | No         |
| 20630-323      | No         |
| 20630-324      | No         |

## ADDITIONAL PRODUCT DETAILS

Varistar CP Base Plate for Rear Cable Ducting, plain for IP 55 or EMC applications.

Please purchase the grounding kit separately.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Europe**

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Asia**

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

**Middle East & India**

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**