

# EuropacPRO 19" Subrack Kit for DIN Connector, Slide Rail, Retrofit Shielding

## Power Utilities



Non-shielded subrack for Din Connector mounting EN 60603-2 , Subrack can be assembled on slide rails to support the subrack inside a cabinet.

## CERTIFICATIONS



## FEATURES

Subrack with side panel type F ("flexible"), 19" bracket with notch for slide rail assembly

Installed load up to 11 kg

Subrack can be used with slide rails

Horizontal rails, rear, for connector mounting (IEC 60603-2 / DIN 41612)

Threaded insert pre-fitted

## SPECIFICATIONS

Table 1/3

| Catalog Number | Rack Height | Depth  | Package Quantity | For Mounting  | Board Depth    | EMC Gasket Type |
|----------------|-------------|--------|------------------|---------------|----------------|-----------------|
| 24553-192      | 3 U         | 235 mm | 1                | DIN Connector | 160 mm, 220 mm | Stainless Steel |

| CatalogNumber | Rack Height | Depth  | Package Quantity | For Mounting  | Board Depth                    | EMC Gasket Type |
|---------------|-------------|--------|------------------|---------------|--------------------------------|-----------------|
| 24553-193     | 3 U         | 295 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm         | Stainless Steel |
| 24553-194     | 3 U         | 355 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm, 340 mm | Stainless Steel |
| 24553-492     | 6 U         | 235 mm | 1                | DIN Connector | 160 mm, 220 mm                 | Stainless Steel |
| 24553-493     | 6 U         | 295 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm         | Stainless Steel |
| 24553-494     | 6 U         | 355 mm | 1                | DIN Connector | 160 mm, 220 mm, 280 mm, 340 mm | Stainless Steel |

Table 2/3

| Catalog Number | Handle Included | Mounting | Complies With   | EMC Shielding | Product Type    | Rack Width |
|----------------|-----------------|----------|-----------------|---------------|-----------------|------------|
| 24553-192      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |
| 24553-193      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |
| 24553-194      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |
| 24553-492      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |
| 24553-493      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |
| 24553-494      | No              | Rack     | IEC 60297-3-103 | No            | Subrack/Chassis | 84 HP      |

Table 3/3

| Catalog Number | Static Load |
|----------------|-------------|
| 24553-192      | 11 kgf      |
| 24553-193      | 11 kgf      |
| 24553-194      | 11 kgf      |
| 24553-492      | 11 kgf      |

| Catalog Number | Static Load |
|----------------|-------------|
| 24553-493      | 11 kgf      |
| 24553-494      | 11 kgf      |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE