


Horizontal Rail, Front, Type R-LD, Rugged, Long Lip , 40 HP

CATALOG NUMBER

34566-340



Combinations of horizontal rails and side panels

$\text{A}^{\text{H}} + \text{C}^{\text{H}}$ can be combined, $\text{A}^{\text{H}} + \text{C}^{\text{H}}$ combination not recommended

RAILS	RAILS	RAILS	RAILS	RAILS
RAILS A ^H		-		not recommended
RAILS B ^H		+		+
RAILS C ^H		+		+
RAILS D ^H		+		+
RAILS E ^H		+		+
RAILS F ^H		+		+
RAILS G ^H		+		+
RAILS H ^H		+		+
RAILS I ^H		+		+
RAILS J ^H		+		+
RAILS K ^H		+		+
RAILS L ^H		+		+
RAILS M ^H		+		+
RAILS N ^H		+		+
RAILS O ^H		+		+
RAILS P ^H		+		+
RAILS Q ^H		+		+
RAILS R ^H		+		+
RAILS S ^H		+		+
RAILS T ^H		+		+
RAILS U ^H		+		+
RAILS V ^H		+		+
RAILS W ^H		+		+
RAILS X ^H		+		+
RAILS Y ^H		+		+
RAILS Z ^H		+		+
RAILS AA ^H		+		+
RAILS AB ^H		+		+
RAILS AC ^H		+		+
RAILS AD ^H		+		+
RAILS AE ^H		+		+
RAILS AF ^H		+		+
RAILS AG ^H		+		+
RAILS AH ^H		+		+
RAILS AI ^H		+		+
RAILS AJ ^H		+		+
RAILS AK ^H		+		

Side panel

RAILS A^H RAILS B^H RAILS C^H RAILS D^H RAILS E^H

The rugged horizontal rail type can handle shock and vibration up to 25 g. It enables the use of IEEE handles.

CERTIFICATIONS



FEATURES

Type R-LD "rugged" horizontal rails with 3-hole fixing for increased robustness

For insertion/extraction of CompactPCI or, VME64x boards

With HP units printed from 28 HP upwards

Length 20, 28, 40, 42, 63, 84 HP or 1000 mm

Aluminum extrusion, anodized finish, conductive contact surface, with HP markings

PRODUCT ATTRIBUTES

Rack Width: 40HP

Package Quantity: 1

Finish: Anodized

Length: 208.28mm

Material: Aluminum

Product Family: EuropacPRO

Product Type: Horizontal Rail

Type: Rugged, LD

Works With: Subracks

Gross Weight: 0.131kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE