


# Guide Rail End Piece, PC

Plastic end pieces for individual multi-piece guide rails with plastic or Aluminum extrusion mid-piece. Available as type Standard or Accessory.



## CERTIFICATIONS



## FEATURES

Guide rail end pieces (PC) for individual multi-piece guide rails with plastic or aluminum extrusion mid-piece

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Mid-pieces available for standard PCB lengths (160, 220, 280 and 340 mm) and for special dimensions as 1000 mm version

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted for higher shock and vibration requirements

Optional ESD clip for an conductive contact between PCB and horizontal rail available

## SPECIFICATIONS

|                        |                                                                                    |
|------------------------|------------------------------------------------------------------------------------|
| <b>Works With:</b>     | Subracks; Cases; Chassis                                                           |
| <b>Product Family:</b> | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac |
| <b>Material:</b>       | Fiber-Reinforced Plastic                                                           |
| <b>Product Type:</b>   | Rail End Piece                                                                     |

Table 1/1

| Catalog Number | Package Quantity | Complies With | Type | Package Unit | Groove Width | Quick Ship |
|----------------|------------------|---------------|------|--------------|--------------|------------|
|----------------|------------------|---------------|------|--------------|--------------|------------|

|           |   |            |            |      |     |    |
|-----------|---|------------|------------|------|-----|----|
| 64568-004 | 1 | EN 45545-2 | Standard   | Pair | 2   | No |
| 64568-008 | 1 | EN 45545-2 | Accessory  | Pair | 2   | No |
| 64568-014 | 1 | EN 45545-2 | Standard   | Pair | 2.5 | No |
| 64568-018 | 1 | EN 45545-2 | Accessory  | Pair | 2.5 | No |
| 64568-093 | 1 | EN 45545-2 | Coding Peg | Pair | 2.5 | No |
| 64568-094 | 1 | EN 45545-2 | Coding Peg | Pair | 2.5 | No |
| 64568-095 | 1 | EN 45545-2 | Coding Peg | Pair | 2.5 | No |

## ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**