

# Varistar CP Steel Door, Plain With 3-Point Locking and Brush Strip, Shortened

Shortened door available for IP20, IP55 applications.



## FEATURES

Height of connection plate 400 mm

Connection plate with brush strip

The height of the door is 400 mm less than the cabinet height

## SPECIFICATIONS

**Locking Type:** 3-Point Locking

**Product Type:** Cabinet Door

**Protection Rating:** IP20

**Material:** Steel

Table 1/2

| Catalog Number | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|----------------|-------------|--------|-------|------------------|------------|------------|
| 21630-352      | 47U         | 2200mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-348      | 38U         | 1800mm | 600mm | 1                | Black Grey | RAL 7021   |
| 21630-353      | 47U         | 2200mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-350      | 42U         | 2000mm | 600mm | 1                | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Height | Width | Package Quantity | Color      | Color Code |
|---------------|-------------|--------|-------|------------------|------------|------------|
| 21630-349     | 38U         | 1800mm | 800mm | 1                | Black Grey | RAL 7021   |
| 21630-351     | 42U         | 2000mm | 800mm | 1                | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Finish        | Quick Ship |
|----------------|---------------|------------|
| 21630-352      | Powder Coated | No         |
| 21630-348      | Powder Coated | No         |
| 21630-353      | Powder Coated | No         |
| 21630-350      | Powder Coated | No         |
| 21630-349      | Powder Coated | No         |
| 21630-351      | Powder Coated | No         |

## ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**