

Outdoor Modular 24 U 1330H 700W 1200D

Data Solutions

CATALOG NUMBER

10149-620



Telecom and Railway applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather and vandalism, ensuring operational continuity. Modular construction allows multiple configurations in size and function along with multiple cooling options.

FEATURES

Aluminium profile frame with removable, double-walled cladding

IP 55 or NEMA 12~

Double-walled

Extensive range of 19" cabinet accessories

Access to cabinet from front, all sides possible upon request

100 mm high plinth, 200 and 300 mm possible

Top cover with louvers, can be upgraded with fans or A/C unit

RAL 7035 powder coating, other colors available upon request

PRODUCT ATTRIBUTES

Product Type: Outdoor Cabinet

Product Family: Modular

Rack Height: 24U

Height: 1330mm

Width: 700mm

Depth: 1200mm

Wall Type: Double Walled

Door Type: Plain; Single Door

Burglar Resistance: Optional

Cooling: Passive

EMC Shielding: Optional

Battery Compartment: Optional

Finish: Powder Coated

Frame Material: Aluminum

Material: Aluminum; Steel

Mounting Setup: Optional

Package Quantity: 1

Plinth Height: 100mm

ADDITIONAL PRODUCT DETAILS

Height dimensions are without base/plinth.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE